



Specifications

Max Load	60W
Input Voltage	120V AC
Input Current Full Load	0.95 A
Output Voltage Full Load	22.2V DC
Max Output Current Full Load	2.56 A
Open Circuit Output Voltage	23.8V DC
Avg. Efficiency	85%
Power Factor on I	0.82
Coil Former	Double Section Bobbin
Thermal Class	B130Oc
Leads Primary	PVC 600V #20
Leads Secondary	PVC 300V #14
Circuit Breaker	primary and secondary auto reset
Dimensions L*W*H	6.55 in. x 2.25 in. x 2.55 in.
Weight	50 Oz.



Features

- Dimmable with any standard MLV TRIAC dimmer
- Dual protection - primary and secondary auto-reset circuit breakers
- Nema 3R Enclosure - Outdoor Use
- Two knock-outs one on each side
- Class 2
- ETL Listed
- Certied to CSA Standard

Revisions:

4		
3		
2		
1		



Project:

Part number: TR24L60DC

Scale: NTS

Product: 24VDC, 60W, DIMMABLE MAGNETIC DRIVER INDOOR / OUTDOOR

Type:

Date: