




GE
Lighting

14639 - GE T6.5

25T6 1/2

Product Photo



GENERAL CHARACTERISTICS

Base Description	Intermediate Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	C-8
Rated Life Hours-nominal	1000 h
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E17
Bulb Shape	T6.5

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	9
Initial Lumens-nominal	220 lm

PRODUCT INFORMATION

Product Code	14639
Description	25T6 1/2
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168146395
Standard Package GTIN	10043168146392
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168146395

DIMENSIONS

Diameter	0.81 in
----------	---------

ELECTRICAL CHARACTERISTICS

Wattage	25 W
Estimated Energy Cost per Year	3.01 \$
Input Voltage [nom]	120 V