



GE
Lighting

14958 - GE G16.5

40GC 12PK

GENERAL CHARACTERISTICS

Base Description	Candelabra Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	CC-2V
Life in Years	1.4 yr
Rated Life Hours-nominal	1500 h
Primary Application	Globe
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E12
Bulb Shape	G16.5

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	320 lm
Color Temperature	2500 K

PRODUCT INFORMATION

Product Code	14958
Description	40GC 12PK
Alternative Unit Of Measure	PACK
Standard Package Quantity	
Ean UPC	043168908986
Standard Package GTIN	00043168149587
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Inner Pack
UCC	043168149587
Alternative Unit Of Measure	EACH
Standard Package Quantity	120
Ean UPC	043168908986
Standard Package GTIN	00043168908986
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	120
Sales Unit	Each
UCC	043168149587
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168908986
Standard Package GTIN	10043168149584
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168149587

DIMENSIONS

Diameter	2.06 in
----------	---------

ELECTRICAL CHARACTERISTICS

Burn Position	Base down to horizontal
Wattage	40 W
Estimated Energy Cost per Year	4.82 \$
Input Voltage [nom]	120 V

CAUTIONS & WARNINGS

Warning

Unexpected lamp rupture may cause injury, fire, or property damage

Avoid direct water

liquid or metal contact.