



Catalog No. TLM812FCUD

Description: 8 CIRC MNLUG 125A INDOOR FLUSH W/DR

UPC No 783164268041

Products > Load Centers > Residential Load Centers > Single Phase - USA

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit www.geelectrical.com

Descriptors

Category	Single Phase - USA
GO Schedule	RD

Specifications

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	65
Amperage	125 A
Device Type	Convertible
Enclosure	Indoor Type 1 Enclosure, Flush Mount
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	0
1" Space	8
1/2" Space	42, 4, 24, 16
Feed	Either
Door	Yes
GSA Compliance	Yes

Publications

Title	Publication No.	Publication Type
8 Circuit Load Center Fact Sheet 2 page data sheet includes product features, photo, catalog number selection table, knockout drawings, conduit size table, wiring diagrams, accessories and options list.	DET-207	Data Sheets
Indoor Load Center 1 page outline drawing in pdf format.	10103091-SH42	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.