



Representative Image

### Catalog No. TL240SCU

Description: 2 CIRC 40A INDOOR SURFACE

UPC No 783164275469

Products > Load Centers > Residential Load Centers > Single Phase - USA

- UL Listed (Panelboards No. 67)
- 60°/75°C Conductor Rating
- Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code
- 22kAIC RMS symmetrical, Except Where Noted
- 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down
- For a listing of CSA Listed load centers, visit [www.geelectrical.com](http://www.geelectrical.com)

### Descriptors

Category	Single Phase - USA
GO Schedule	RD

### Specifications

Input/Output Voltage	120/240V ac
Type	Standard
Interrupting Capacity Rating	65
Amperage	40 A
Device Type	Main Lugs
Enclosure	Indoor Type 1 Enclosure, Surface Mount
UL/CUL Listing	UL
Phase	1 Phase
Socket Type	0
1" Space	2
1/2" Space	4
Feed	Either
Door	No
GSA Compliance	Yes

## Publications

Title	Publication No.	Publication Type
<a href="#">Outline Drawing</a>	10103091-SH47	Drawings-Outline and Dimensional
1 page outline drawing in pdf format.		
<a href="#">8 Circuit Load Center Fact Sheet</a>	DET-207	Data Sheets
2 page data sheet includes product features, photo, catalog number selection table, knockout drawings, conduit size table, wiring diagrams, accessories and options list.		

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.