

Electrical Commercial and Industrial

Products | Documentation & Literature | News & Tradeshow s | Support

United States > Energy > Electrical Commercial and Industrial > Products > Electrical Commercial & Industrial Products Catalog > Electrical Tape, Mastics & Special Use > Rubber Tapes - Insulating and Splicing > 3M™ Linerless Electrical Rubber Tape 2242, 1 1/2 in x 15 ft (38 mm x 4,6m), 12 per case

Find An Account Rep

Where To Buy (Find A Distributor)

Contact Us

3M™ Linerless Electrical Rubber Tape 2242, 1 1/2 in x 15 ft (38 mm x 4,6m), 12 per case

3M ID 80610922967 UPC# 00054007413233 Part Number 2242-1-1/2X15FT

• Print



3M™ Linerless Splicing Compound 2242 is a highly conformable, linerless Ethylene Propylene Rubber-based tape.

Need Help?

Questions? We can help
[Contact Us](#)



Overview

Documents

3M™ Linerless Electrical Rubber Tape 2242 is used for all-voltage splicing, jacketing, & general insulating.

Specifications

Adhesive Material	Rubber Resin
Agency Approvals	HH-I-553C, ASTM D-4388 Type 1, 2 & 3
Backing Material	Rubber
Brand	3M
Breaking Strength	7.5 lb/in
Color	Black
Dielectric Strength (V/mil)	750 V/mil
Emergency Overload Temperature (Celsius)	130 Degree Celsius
Emergency Overload Temperature (Fahrenheit)	266 Degree Fahrenheit
Family	3M™ Linerless Splicing Compound 2242
Length	15 Linear Foot
Material	Self-fusing Ethylene Propylene Rubber (EPR)
Operating Temperature (Celsius)	90 Degree Celsius
Operating Temperature (Fahrenheit)	194 Degree Fahrenheit
Product Family	3M™ Linerless Splicing Compound 2242

RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Rolls per Carton	1
Rolls per Case	12
Tape Grade	Premium
Tape Type	Rubber Insulating and Splicing
Tensile Strength	250 Pound-Force Per Square Inch
Tensile Strength lb/in (N/100 mm)	7.5 (131)
Thickness	30 mil
Trademark	Scotch
Width	1.5 Inch

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.