



## 61375-839: One Light Mini-Pendant



**Collection:** Somerton

Mini-Pendant in Blacksmith Finish with Cafe Tint Glass Shade

for Additional Stems, Order 9199-839; Three 12 inch stems, chain, and canopy included

**UPC #:**785652613708

**Finish:** Blacksmith (839)

### Dimensions:

**Diameter:** 9"

**Height:** 7 3/4"

**Weight:** 3.8 lbs.

**Overall Height:** 60 1/4"

**Wire:** 120" (color/Black)

**Chain:** 12"

**Mounting Proc.:** Center Lock-Up

**Connection:** Mounted To Box

### Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

### Features:

- A decorative canopy is included
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

### Material List:

- 1 Body - Steel - Blacksmith
- 1 Chain - Steel - Blacksmith
- 3 12" Stem - Steel - Blacksmith

### Safety Listing:

- Safety Listed for Dry Locations
- Safety Listed for Dry Locations

### Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1122FS)

### Shade / Glass / Diffuser Details:

| Part  | Material | Finish    | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|-------|----------|-----------|----------|-------------|--------|-------|--------|----------|-----------------|------------------|-----------------|--------------------|
| Shade | Glass    | Cafe Tint | 1        |             |        |       |        | 9        |                 |                  |                 |                    |

### Backplate / Canopy Details:

| Type   | Height / Length | Width | Depth | Diameter | Outlet Box Up | Outlet Box Down |
|--------|-----------------|-------|-------|----------|---------------|-----------------|
| Canopy | 1               |       |       | 5 1/2    |               |                 |

### Replacement Bulb Data:

| Product # |         |  | Type | Base        | Watts | Watts Consumed | Volts | Hours | Lumens | Temp (°K) | CRI |
|-----------|---------|--|------|-------------|-------|----------------|-------|-------|--------|-----------|-----|
| 97308S    | Frosted |  | A19  | E-26 Medium | 8     | 8              | 120v  | 50000 | 450    | 3000      | 85  |
| 97408S    | Frosted |  | A19  | E-26 Medium | 8     | 8              | 120v  | 50000 | 450    | 2700      | 85  |
| 97309S    | Frosted |  | A19  | E-26 Medium | 13.5  | 13.5           | 120v  | 50000 | 800    | 3000      | 85  |
| 97409S    | Frosted |  | A19  | E-26 Medium | 13.5  | 13.5           | 120v  | 50000 | 800    | 2700      | 85  |

### Shipping Information:

| Package Type | Product # | Quantity | UPC          | Length | Width | Height | Cube  | Weight | Fr. Class | UPS Ship |
|--------------|-----------|----------|--------------|--------|-------|--------|-------|--------|-----------|----------|
| Individual   | 61375-839 | 1        | 785652613708 | 11.5   | 11    | 8.75   | 0.641 | 4.7    | 125       | Yes      |

|           |  |     |  |    |    |      |        |       |  |    |
|-----------|--|-----|--|----|----|------|--------|-------|--|----|
| NJ Pallet |  | 102 |  | 48 | 40 | 71.5 | 79.444 | 479.4 |  | No |
| NV Pallet |  | 102 |  | 48 | 40 | 71.5 | 79.444 | 479.4 |  | No |