



GE
Lighting

**15834 - GE Soft White Spiral® T3 - Facilities; Retail Display;
Hospitality; Office; Restaurant**

FLE20HT3/2/827

- ☞ Up to 75% energy savings
- ☞ One piece unit screws directly into incandescent sockets
- ☞ T3 Spirals® lamps provide economical solution with small overall size
- ☞ Long life -8000-12,000 hour rating

Product Photo



GENERAL CHARACTERISTICS

Base Type	Screw-In
Mercury Content	1.8 mg
Rated Life Hours-nominal	10000 h
Starting Temp (MIN) C-degrees	-15 °C
Base Description	Medium Screw
Mercury-Picogram per mean lm hr	233.2
Primary Application	Standard <General Purpose> Facilities Retail Display Hospitality Office Restaurant

Product Technology	Compact Fluorescent
Base	E26
Bulb Shape	T5

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	965 lm
Nominal Initial Lumen per Watt	60
Initial Lumens-nominal	1200 lm
Color Rendering Index-CRI	82
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	15834
Description	FLE20HT3/2/827
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168158343
Standard Package GTIN	10043168158340
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168158343
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168158343
Standard Package GTIN	00043168158343
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168158343

DIMENSIONS

Nominal Length	4.7 in
Bulb Max Overall Length-MOL	4.7 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	75 W
Rated power (Watts)	20 W

CAUTIONS & WARNINGS

NOTES

Best performance if operated base up and at 77 degrees F (25C) ambient temperature.