



GE
Lighting

15852 - GE T10

40T10

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Finishes and Colors	Clear
Filament	C-8
Life in Years	0.9 yr
Rated Life Hours-nominal	1000 h
Primary Application	Standard <General Purpose> Standard <Decorative>
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E26
Bulb Shape	T10

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	11
Initial Lumens-nominal	420 lm
Color Temperature	2500 K

PRODUCT INFORMATION

Product Code	15852
Description	40T10
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168158527
Standard Package GTIN	10043168158524
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168158527

DIMENSIONS

Diameter	1.25 in
----------	---------

ELECTRICAL CHARACTERISTICS

Wattage	40 W
Estimated Energy Cost per Year	4.82 \$
Input Voltage [nom]	120 V