

INSTRUMENTATION CABLE

Twisted Pairs -300 Volt
Individually Shielded
S-R PVC Insulation -80C



CONSTRUCTION	
Conductor	- Stranded tinned copper
Insulation	- S-R PVC insulation with twisted pairs
Shield	- Each pair individually shielded with 100% aluminum/polyester shield and 22 AWG stranded tinned copper drain wire
Jacket	- Gray PVC

COLOR CODE CHART	
Pairs	Color
1	Red & Black
2	Green & White

Applications:

- Audio and control cable

Standards:

- UL AWM 2464
- NEC type CMG
- 300 Volt rated
- 80°C rated

Part #	AWG	Pairs	Stranding	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
D32002	20	2	7x8 TC	.010"	.041"	.301"	43

* Capacitance between conductors

** Capacitance between one conductor and other conductors connected to shield