

Electrical Commercial and Industrial

Products | Documentation & Literature | News & Tradeshows | Support

United States > Energy > Electrical Commercial and Industrial > Products > Electrical Commercial & Industrial Products Catalog > Electrical Tape, Mastics & Special Use > Vinyl Electrical Tapes > 3M™ Temflex™ General Use Vinyl Electrical Tape 1700C, 3/4 in x 66 ft, Orange

[Find An Account Rep](#)

[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

3M™ Temflex™ General Use Vinyl Electrical Tape 1700C, 3/4 in x 66 ft, Orange

3M ID 80610736920 UPC# 00054007506522 Part Number 1700C-ORANGE



3M™ Temflex™ Tape 1700C is a 7-mil thick, excellent quality, general-purpose, vinyl electrical tape. This flame-retardant tape is designed for protective jacketing and harnessing. This tape is 600V-rated and withstands a temperature range of 32 to 176 degrees F (0 to 80 degrees C).

- The combination of the rubber-resin adhesive and the flame-retardant, PVC backing offers electrical and mechanical protection
- Provides resistance to abrasion, moisture, alkalis, solvents and other varying weather conditions
- For protective jacketing and harnessing
- Tape measures 3/4 in x 66 ft x 7 mil
- Made of orange durable PVC
- Withstands a temperature range of 32 to 176 degrees F (0 to 80 degrees C)
- UL Listed, ASTM Approved, CSA Certified and RoHS 2011/65/EU Compliant
- 100 rolls/case

• Print

Need Help?

Questions? We can help
[Contact Us](#)

Overview	Documents
3M™ Temflex™ Tape 1700C Electrical Tape provides electrical and mechanical protection with the combination of an aggressive, rubber-resin adhesive and flame-retardant, highly conformable, PVC backing. This tape is highly resistant to abrasion, moisture, alkalis, acid, copper corrosion and varying weather conditions. UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.	
Specifications	
Adhesive Material	Rubber Resin
Agency Approvals	CSA Certified, UL Listed
Backing Material	Polyvinyl Chloride
Brand	Temflex™
Breaking Strength	17 lb/in
Color	Orange
Dielectric Strength	1000 V/mil
Length	66 Linear Foot
Length (Metric)	20.1 m
Operating Temperature Range (Celsius)	0 to 80 Degree Celsius
Operating Temperature Range (Fahrenheit)	32 to 176 Degree Fahrenheit
RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Specifications	ASTM D 2301 Type 1
Tape Grade	General Use
Tape Type	Vinyl
Thickness	7 mil

Thickness (Metric)	0.177 mm
Voltage Application	Low Voltage
Width	0.75 Inch
Width (Metric)	19 mm