



GE
Lighting

16741 - GE G40

60G40/W CPK

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Finishes and Colors	White
Filament	CC-6
Life in Years	2.3 yr
Rated Life Hours-nominal	2500 h
Primary Application	Globe
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E26
Bulb Shape	G40

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	660 lm
Color Temperature	2600 K

PRODUCT INFORMATION

Product Code	16741
Description	60G40/W CPK
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168167413
Standard Package GTIN	10043168167410
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168167413
Alternative Unit Of Measure	EACH
Standard Package Quantity	24
Ean UPC	043168167413
Standard Package GTIN	00043168167413
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
Sales Unit	Each
UCC	043168167413

DIMENSIONS

Diameter	5.0 in
----------	--------

ELECTRICAL CHARACTERISTICS

Wattage	60 W
Estimated Energy Cost per Year	7.23 \$
Input Voltage [nom]	120 V