



GE  
Lighting

### 16751 - GE halogen 50 watt MR16 1-pack

#### Q50GU10/FL/CD

- Edison™ halogen bulbs provide a brighter, crisper light that makes your home look its best
- That's why professionals choose Edison for exceptional results and longer bulb life.
- Showcase the beauty of your home with the highest quality of light.
- Estimated yearly energy costs \$6.02 based on 3 hours per day \$0.11 per kWh
- Lasts 2.7 years based on 3 hours per day usage
- MR16 shape with GU10 base for use directional fixtures such as recessed can lighting
- GE halogen bulbs deliver crisp, white light. This unsurpassed light quality is ideal for adding depth, drama and interest inside and outside your home. Use GE halogen MR16 bulbs in indoor track and recessed lighting and outdoor directional lighting to create a dramatic effect
- Input Voltage = 120 volts

#### Product Photo



#### CAUTIONS & WARNINGS

##### Caution

- Lamp may shatter and cause injury if broken
- Dispose of lamp in a closed container.
- Do not use lamp if outer glass is scratched or broken.

##### Warning

###### Risk of Burn

- Allow lamp to cool before handling.

A damaged lamp emits UV radiation which may cause eye/skin injury

- Turn power off if glass bulb is broken. Remove and dispose of lamp.

###### Risk of Electric Shock

- Turn power off before inspection
- installation or removal.

Pressurized lamp--unexpected rupture may cause injury, fire, or property damage

- Do not exceed rated voltage.
- Do not use lamp if outer glass is scratched or broken.

###### Risk of Fire

#### GENERAL CHARACTERISTICS

|                          |                   |
|--------------------------|-------------------|
| Base Type                | Pin/Plug-In       |
| Filament                 | CC-2V             |
| Rated Life Hours-nominal | 3000 h            |
| Primary Application      | Indoor Floodlight |
| Product Technology       | Halogen           |
| Base                     | GU10              |
| Bulb Shape               | MR16              |

#### PHOTOMETRIC CHARACTERISTICS

|                                |         |
|--------------------------------|---------|
| Center Beam Candle Pwr Candela | 1000 cd |
| Initial Lumens-nominal         | 400 lm  |
| Color Temperature              | 2750 K  |

#### PRODUCT INFORMATION

|                                  |                |
|----------------------------------|----------------|
| Product Code                     | 16751          |
| Description                      | Q50GU10/FL/CD  |
| Alternative Unit Of Measure      | Case           |
| Standard Package Quantity        | 5              |
| Ean UPC                          | 043168167512   |
| Standard Package GTIN            | 10043168167519 |
| No Of Items Per Sales Unit       | 1              |
| No Of Items Per Standard Package | 5              |
| Sales Unit                       | Unit           |
| UCC                              | 043168167512   |

#### DIMENSIONS

|          |      |
|----------|------|
| Diameter | 2 in |
|----------|------|

#### ELECTRICAL CHARACTERISTICS

|                     |       |
|---------------------|-------|
| Input Voltage [nom] | 120 V |
| Rated power (Watts) | 50 W  |

In table lamp

use only with shade.

Keep combustible materials away from lamp.

Use in fixture rated for this product.

Sep 30, 2015 10:01:08 AM For additional information, visit [www.gelighting.com](http://www.gelighting.com)