



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YAV28L2NTCFX  
 7818100220855  
 CU HYLUG-4/0 FLEX-NEMA  
 Active

**Web Use**  
 BURNDY Product Line

Tongue Angle  
 Length (in)  
 Tongue Type  
 Barrell Style  
 Bolt Hole Size (in)  
 Barrel Type  
 Thickness  
 B Length (in)  
 Pad Width (in)  
 E - in  
 Strip Length

**Dimensional**

Straight  
 4.62  
 Standard  
 Chamfered,Skived  
 0.52  
 Standard  
 0.15  
 1.03  
 1.14  
 1.75  
 1-1/16

Number of Holes  
 Product Description

**General**

2  
 Copper Compression Lug, 2 Hole  
 w/ Inspection Window, 4/0 Flex,  
 1/2" Stud, 1-3/4" Stud Hole  
 Spacing, Short Barrel, Tin Plated

Flex (Class G) Size - Range  
 Flex (Class H) Size - Range  
 Flex (Class I) Size - Range  
 Copper Solid Size (Range)  
 DLO Size (Range)  
 Copper Stranded (Range)

**Conductor(s)**

4/0 AWG  
 4/0 AWG  
 4/0 AWG  
 N/A  
 4/0 (550/#24) DLO  
 4/0 AWG

Type of Plating  
 Bolt Hole Size  
 Color Code  
 Plated (Yes or No)  
 Index Number  
 Product Material

**Physical**

Tin  
 1/2  
 Purple  
 Y  
 15  
 Copper

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS

**Approvals / Certifications**

Y  
 Y  
 Compliant  
 N  
 N

**Documentation**

For further technical assistance, please contact us

47 East Industrial Park Drive  
Manchester NH 03109

47 East Industrial Park Drive  
Manchester NH 03109

Phone: 800-346-4175