



BURNDY Catalog Number YAV28LTC38FX
 UPC Number 781810021934
 Description CU HYLUG-4/0 FLEX-3/8\"S
 Status Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Strip Length	1-1/16
Length (in)	2.42
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.15
B Length (in)	1.03
Pad Width (in)	1.14
General	
Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 4/0 Flex, 3/8" Stud, Short Barrel, Tin Plated
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	4/0 AWG
Physical	
Type of Plating	Tin
Bolt Hole Size	3/8
Color Code	Purple
Plated (Yes or No)	Y
Index Number	15
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175