




C1.5LG6



- Choose from 16 sizes of *PANDUIT* covers from 0.5" to 6" (25mm to 100mm). The non-slip design snaps onto the duct to conceal the wiring and improve the appearance of your control panel.
- Non-slip cover design incorporates integral high friction lining to inhibit cover movement
- Cover flush with base provides greater wire capacity and improves aesthetics
- Easy cover removal makes changes to wiring quick and easy
- Available in various colors

• Part Number	C1.5LG6
• RoHS Compliancy Status	Compliant
• Part Description	Covers duct to protect wires, improve aesthetics and provides greater wire capacity.
• Material	Lead-free PVC
• Color	Light Gray
• Length (ft.)	6
• Length (m)	1.82
• Pricing Description	Duct Cover, PVC, 1.5"W X 6', LGray
• Min. Order UOM	FT
• Min. Order Qty.	6
• BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOMINAL DUCT SIZE (W)	C in (mm)	TC in (mm)	HC in (mm)
.5	.69 (17.5)	.040 (1.0)	.230 (5.8)
.75	.94 (23.8)	.050 (1.3)	.240 (6.1)
1	1.25 (31.8)	.060 (1.5)	.350 (8.9)
1.5	1.75 (44.5)	"	"
2	2.25 (57.2)	"	"
2.5	2.75 (69.9)	"	"
3	3.25 (82.6)	.065 (1.6)	.370 (9.4)
4	4.25 (108.0)	"	"
6	6.25 (158.8)	.080 (2.0)	"

PART NO. SYSTEM COVER EXAMPLE

C 1.5 LG 6
 TYPE WIDTH COLOR LENGTH (ft)

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESIS ARE METRIC.

CAD FILENAME/LAYERS

D34518BA_PVC_COVER_02A

PANDUIT

TINLEY PARK, ILLINOIS

WIRING DUCT COVER FOR DUCT TYPES "S", "D", "E", "F", "FS", AND "G" CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (".XX") : ANGLES : UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

MAT'L: POLYVINYL CHLORIDE

SCALE: NONE

DRAWING NO. 34518-17

SIZE: A

DRAWN BY: DW
 DATE: 10-29-93
 CHK'D: CEF

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	8-24-01	JCST	JKG	D: CHANGED TOLERANCE MADE "C" A REFERENCE DIMENSION	34518-17	JKG	JKG	
1	2/11/00	JHNU	HIW	B: .18 WAS .125/ 4.5 WAS 3.2 A: REV'D TITLE; ADDED FS AND G DUCT TYPE	34518-17	HIW	HIW	
R	10-29-93	DW	CEF	RELEASED TO PRODUCTION.	34518-17	CEF	CEF	