



31146-814: Six Light Chandelier



Collection: Acadia

Six Light Chandelier in Misted Bronze Finish with Champagne Seeded Glass Shades

European Rustic combines comfort and sophistication. The Misted Bronze is a mix of dark & russet browns that suggests warmth. The Champagne Seeded glass creates soft romantic glows.

UPC #: 785652311468

Finish: Misted Bronze (814)

Dimensions:

Diameter: 26 1/4"

Height: 26 1/4"

Overall Height: 64 3/4"

Wire: 144" (color/Brown)

Chain: 36"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

6 - Medium A19 100w Max. 120v - Not included
6 - LED Medium A19 8w Max. 120v - Not included
6 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- A decorative canopy is included
- Easily converts to LED with optional replacement lamps

Material List:

1 Body - Steel - Misted Bronze

1 Chain - Steel - Misted Bronze

Safety Listing:

Safety Listed for Dry Locations
Safety Listed for Dry Locations

Instruction Sheets:

English (HC-1000)

French (F-004)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Champagne Seeded	6					5 1/16				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1 1/2	5 1/4		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	31146-814	1	785652311468	26	13	26.25	5.135	26.9	150	Yes
NJ Pallet		9		48	40	72	80	242.1		No

NV Pallet		8		48	40	69	76.667	196		No
-----------	--	---	--	----	----	----	--------	-----	--	----