



61940-962: One Light Mini-Pendant



Collection: Windgate

One Light Mini-Pendant in Brushed Nickel Finish with Alabaster Glass Shade

Includes three interconnecting 12" stems and one 6" stem

UPC #:785652028601

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 7 1/2"

Height: 6 1/2"

Overall Height: 51"

Wire: 96"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Sloped ceiling mounting hardware included
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

- 1 Body - Steel - Brushed Nickel
- 1 6" Stem - Steel - Brushed Nickel
- 3 12" Stem - Steel - Brushed Nickel

Safety Listing:

- Safety Listed for Dry Locations
- Safety Listed for Dry Locations

Instruction Sheets:

Bilingual (English - French) (HC-1712FB)

Shade / Glass / Diffuser Details:

| Part | Material | Finish | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|-------|----------|-----------|----------|-------------|--------|-------|--------|----------|-----------------|------------------|-----------------|--------------------|
| Shade | Glass | Alabaster | 1 | | | | 4 7/8 | 7 7/16 | 1 5/8 | | | |

Backplate / Canopy Details:

| Type | Height / Length | Width | Depth | Diameter | Outlet Box Up | Outlet Box Down |
|--------|-----------------|-------|-------|----------|---------------|-----------------|
| Canopy | 7/8 | | | 5 | | |

Replacement Bulb Data:

| Product # | | | Type | Base | Watts | Watts Consumed | Volts | Hours | Lumens | Temp (°K) | CRI |
|-----------|---------|--|------|-------------|-------|----------------|-------|-------|--------|-----------|-----|
| 97308S | Frosted | | A19 | E-26 Medium | 8 | 8 | 120v | 50000 | 450 | 3000 | 85 |
| 97408S | Frosted | | A19 | E-26 Medium | 8 | 8 | 120v | 50000 | 450 | 2700 | 85 |
| 97309S | Frosted | | A19 | E-26 Medium | 13.5 | 13.5 | 120v | 50000 | 800 | 3000 | 85 |
| 97409S | Frosted | | A19 | E-26 Medium | 13.5 | 13.5 | 120v | 50000 | 800 | 2700 | 85 |

Shipping Information:

| Package Type | Product # | Quantity | UPC | Length | Width | Height | Cube | Weight | Fr. Class | UPS Ship |
|--------------|-----------|----------|--------------|--------|-------|--------|--------|--------|-----------|----------|
| Individual | 61940-962 | 1 | 785652028601 | 10 | 7.5 | 13.75 | 0.597 | 3.8 | 125 | Yes |
| NJ Pallet | | 120 | | 48 | 40 | 77 | 85.556 | 456 | | No |

| | | | | | | | | | | |
|-----------|--|-----|--|----|----|------|--------|-------|--|----|
| NV Pallet | | 108 | | 48 | 40 | 72.5 | 80.556 | 410.4 | | No |
|-----------|--|-----|--|----|----|------|--------|-------|--|----|