



Specification Sheet

T6 1/2 Specialty Incandescent Lamp

Order Number **03705**

Specifications

Energy Used (Watts).....	25
Domestic Code.....	25T61/2/IN
Volts.....	120
Brightness (Lumens)	185
Average Rated Hours	1000
Life (in years)*	0.9
Dimmable.....	Yes
Filament Type	C8
Light Center Length (LCL)	3 5/16"
Estimated Yearly Energy Cost**	\$3.01
Country of Origin	China

Physical Characteristics

Finish	Clear
Base	Intermediate
MOL.....	5 3/8"



* Based on 3 hrs./day

* * Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee
© "Westinghouse" and "You can be sure...if it's Westinghouse" are all registered trademarks of Westinghouse Electric Corporation.

