



44350-965: Two Light Wall / Bath



Collection: Laurel Leaf

Two Light Bath Bar in Antique Brushed Nickel Finish with Etched Ripple Glass Shades with Antique Brushed Nickel Bands

UPC #: 785652443558

Finish: Antique Brushed Nickel (965)

Dimensions:

Width:	15"	Extends:	7 1/4"
Height:	9 1/4"	Wire:	6 1/2"
Weight:	3.9 lbs.	Mounting Proc.:	Center Lock-Up
		Connection:	Mounted To Box

Bulbs:

- 2 - Medium A19 100w Max. 120v - Not included
- 2 - LED Medium A19 8w Max. 120v - Not included
- 2 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Fixture may be mounted in the up or down position
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Antique Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1085FS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Etched Ripple	2					5 9/16				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	5	9	1		5	4 1/4

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	44350-965	1	785652443558	13.75	10.25	10.5	0.856	4.8	150	Yes
NJ Pallet		72		48	40	68	75.556	345.6		No
NV Pallet		72		48	40	68	75.556	345.6		No