

Item #
350

Product Family Name:

Category:
WALL SCONCE

Certification
3057374

Patents:

Notes:

UPC Code:
747396002590

Finish:
Bisque White

Category Type:
Sconce



Image File Name: **350.jpg**



MEASUREMENTS

Width: 12.5	Length: Min Overall Height:	Height: 5.5 Max Overall Height:	Extension: 6 Slope: No
Wire Length: 7"	Chain Length:	Safety Cable Included: No	Net Weight: 2.73
Canopy Width:	Canopy Height:	Canopy Length:	Center to Bottom: 2.63
Backplate Width: 12.38	Backplate Height: 5.5	Center to Top: 2.88	

LAMPING

No. of Bulbs: 1	Light Type: A-19, MED			
Max Bulb Wattage: 100	Socket: E26, MED			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: No	Bulb/LED Included:
Bulb/LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: CERAMIC
Part No.: G350	Quantity: 1
Width: 12.38	Height: 5.5
	Length:



SHIPPING

Carton Width: 7.75	Carton Height: 7.0	Carton Length: 14.25
Carton Weight: 3.52	Carton Cubic Feet: 0.447	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1
		Master Pack: 1



Damp
Location



Title 17



ETL
Intertek



WARNING: Handling this product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. Wash hands with soap and water after installing, handling, cleaning or otherwise touching this product. For more information go to: www.P65Warnings.ca.gov.

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.