

2RC10

Sta-Kon[®]

Nylon insulated splice - Butt type - insulation support. Wire range of 12-10

RBB T&B-RBB

General

Type:	Butt Splices
T&B UPC:	78621080022
T&B Status:	M
Colour:	Yellow
Crimping Tool:	ERG4001
Material:	Copper

Dimension Information

Wire Size:	12-10 AWG
------------	-----------