



Actual



Actual

Catalog Number: RB14-10
Product ID: 7TAI029810R0009
UPC Number: 78621080412
EAN Number: 05414363158288
Status: Active

Nylon Insulated Ring Terminal, Length .89 Inches, Width .31 Inches, Maximum Insulation .162, Bolt Hole #10, Wire Range #18-#14 AWG, Color Blue, Copper, Tin Plated

- Self-insulated with high dielectric-strength nylon sleeves.
- An inner bronze insulation grip sleeve lengthens the flexing radius of the conductor and eliminates conductor creep.
- Application Tools: WT2000, WT112M, WT145C, ERG4001, WT145A
- Alternate Package Qty: RB873

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	Self-insulated with high dielectric-strength nylon sleeves. An inner bronze insulation grip sleeve lengthens the flexing radius of the conductor and eliminates conductor creep.
Standard	UL E9809
Wire Size	18-14
Voltage Rating	600V
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Blue
Reel packaging	N
AWG-range	18-14
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	100
Inner Dimensions (inches)	6x2.3x3.1
Outer Quantity	500
Outer Dimensions (inches)	14.9x9.4x8.8
Weight Uom	1.88 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321

