



S4485

KX60FR/3M/E12

60 watt; Halogen / Excel; T3; Frosted; 3000 Average rated hours; 950 Lumens; Candelabra base; 120 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S4485

Item Number	Product Line	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base
S4485	EXCEL	045923044854	60	120	T3	Candelabra	E12
Lamp Code	Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color
KX60FR/3M/E12	Frost	2-7/16"	0.38"	CC-8	950	2900	Warm White
Average Rated Hours	Pack	Package Type	Dimmable/Non-Dimmable		RoHS Compliant		
3000	10	Box	Dimmable		Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

