

FA36100

FA/LA MOLDED CASE CIRCUIT BREAKER, 600V, 100A, 3P

Product availability : Stock - Normally stocked in distribution facility



Price* : 1163.00 USD



Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Thermal-magnetic
Breaking capacity code	A

Complementary

Line Rated Current	100 A
Poles description	3P
Breaking capacity	10 kA at 250 V DC 25 kA at 120/240 V AC 18 kA at 277/480 V AC 14 kA at 347/600 V AC
System Voltage	250 V DC 600 V AC
Mounting mode	I-Line
Electrical connection	I-Line connection line Lugs load
AWG gauge	AWG 14...AWG 4 (copper) 1 cable(s) AWG 12...AWG 4 (aluminium) 1 cable(s)
Terminal identifier	AL50FA
Magnetic hold current	900 A
Magnetic tripping current	1700 A
Phase connection	ABC


Environment

Product certifications	CSA UL listed
------------------------	------------------

Ordering and shipping details

Category	01010 - FA/FH 600V
Discount Schedule	DE2
GTIN	00785901429487
Nbr. of units in pkg.	1
Package weight(Lbs)	6.219999999999998
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1304 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------