



## 8869-12: One Light Outdoor Ceiling Flush Mount



**Collection:** Sebring

Outdoor Close to Ceiling Fixture Finished in Black with Clear Seeded Glass.

Eye-catching style, in a black finish over solid aluminum. Clear seeded glass adds just the right sparkle.

**UPC #:**785652886928

**Finish:** Black (12)

### Dimensions:

**Diameter:** 11 1/4"

**Height:** 9 1/4"

**Weight:** 2.4 lbs.

**Wire:** 6 1/2" (color/Black/White)

**Mounting Proc.:** Cap Nuts

**Connection:** Mounted To Box

**Bulb Appearance:** Clear

### Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

### Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

### Material List:

1 Body - Aluminum - Black

### Safety Listing:

Safety Listed for Damp Locations  
Safety Listed for Damp Locations

### Instruction Sheets:

English (HC-533)  
French (F-002)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Clear Seeded	1	G500319-67			6 5/8	5				

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1			6 5/16		

### Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8869-12	1	785652886928	14	13.25	10.58	1.136	3.5	250	Yes
NJ Pallet		54		48	40	70	77.778	189		No

NV Pallet		54		48	40	75	83.333	189		No
-----------	--	----	--	----	----	----	--------	-----	--	----