



GE
Lighting

26591 - GE T3.25 (T3 1/4) - Low Voltage

755

GENERAL CHARACTERISTICS

Base Type	Pin/Plug-In
Base Description	Miniature Bayonet
Filament	C-2R
Bulb Material	Hard glass
Rated Life Hours-nominal	20000 h
Atmosphere	Vacuum
Primary Application	Low Voltage
Base	Ba9s
Bulb Shape	T3.25 (T3 1/4)

PHOTOMETRIC CHARACTERISTICS

Mean Spherical Candlepower	0.330 cd
Nominal Initial Lumen per Watt	4
Initial Lumens-nominal	4 lm

PRODUCT INFORMATION

Product Code	26591
Description	755
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168265911
Standard Package GTIN	10043168265918
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168265911

DIMENSIONS

Diameter	0.4 cm
Light Center Length (LCL)	0.78 cm
Bulb Max Overall Length-MOL	1.19 cm

ELECTRICAL CHARACTERISTICS

Input Voltage [nom]	6.3 V
Rated power (Watts)	1 W

