


8400-W




Color:



White

UPC Code: 07847749257

NEMA:
6-20R



8400-W

Brand Features

All Leviton Hospital Grade Receptacles undergo the most stringent UL testing to assure continuous, safe operation in any application requiring high-abuse tolerance, including health care facilities, manufacturing plants and schools.

Item Description

20 Amp, 250 Volt, NEMA 6-20R, 2P, 3W, Wide Body Duplex Receptacle, Straight Blade, Hospital Grade, Self Grounding, , Back & Side 8 Hole Feed-Thru Wired, Brass Strap - WHITE

Technical Information

AC Horsepower Ratings

Horsepower Rating: 2 HP

Electrical Specifications

Dielectric Voltage: Withstands 2000V per UL498

Grounding: Self-Grounding

Temperature Rise: Max 30C after 250 cycles OL at 200 percent rated current

Voltage: 250 Volt

Amperage: 20 Amp

Current Limiting: Full Rated Current

Wire: 3

Pole: 2

Environmental Specifications

Operating Temperature: -40C to 60C

Flammability: Rated V-2 per UL94

Material Specifications

Strap Material: Brass

Face Material: Nylon

Body Material: Nylon

Ground Clips: Nickel-Plated Brass

Terminal Screws: Nickel-Plated Brass
10-32

Color: White

Line Contacts: Nickel-Plated Brass
Triple-Wipe .031 Thick

Grounding Screw: Nickel-Plated Brass
8-32

Clamp Nuts: Nickel-Plated Brass

Mechanical Specifications

Product ID: Ratings are permanently marked on device

Terminal ID: Brass-Hot, Green-Ground, Silver-Neutral

Terminal Accom.: 14-10 AWG

Product Features

Color: White

NEMA: 6-20R

Standards and Certifications

UL498HG: File E13399

Warranty: 10 Year Limited

CSA C22.2 No. 42: File 152105


UL Fed Spec WC-596: File E13399

ANSI: C-73


NOM: 057

NEMA: WD-6

Dimensional Diagram



Wiring Diagram



6-20R

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

