



GE  
Lighting

### 34715 - GE halogen 20 watt T3 1-pack

TU\*M47/H Q20/12V/TR/CL G4 GE BX 1/20 MIH

- 12 volts
- GE halogen bulbs deliver crisp, white light. This unsurpassed light quality is ideal for adding depth, drama and interest to any room or space. Use GE halogen specialty bulbs to create a dramatic effect
- Lasts 1.8 years based on 3 hours per day usage
- T3 shape with 2-Pin (G4) base for use in outdoor carriage and post lights

### Product Photo



### GENERAL CHARACTERISTICS

Base Description	2-Pin
Base Type	Pin/Plug-In
Filament	C-6
Rated Life Hours-nominal	2000 h
Product Technology	Halogen
Base	G4
Bulb Shape	T3

### PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	18
Initial Lumens-nominal	350 lm

### PRODUCT INFORMATION

Product Code	34715
Description	TU*M47/H Q20/12V/TR/CL G4 GE BX 1/20 MIH
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168347150
Standard Package GTIN	30043168347151
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168347150
Alternative Unit Of Measure	EACH
Standard Package Quantity	100
Ean UPC	043168347150
Standard Package GTIN	00043168347150
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	100
Sales Unit	Each
UCC	043168347150

### DIMENSIONS

Diameter	0.37 in
Light Center Length	0.75 in

### ELECTRICAL CHARACTERISTICS

Input Voltage [nom]	12 V
Rated power (Watts)	20 W

### CAUTIONS & WARNINGS

#### Caution

- Lamp may shatter and cause injury if broken
- Dispose of lamp in a closed container.
- Do not use lamp if outer glass is scratched or broken.

#### Warning

##### Risk of Burn

- Allow lamp to cool before handling.
- Turn power off before installing lamp.

##### Risk of Fire

- Keep combustible materials away from lamp.
- Use in enclosed fixture rated for this product.

Pressurized lamp--unexpected rupture may cause injury, fire, or property damage

- Do not touch glass with bare hands.
- Do not use lamp if outer glass is scratched or broken.
- Use in enclosed fixture rated for this product.

