

Rustic Collection
 Rustic 1 Light Outdoor Wall Light - RST
 9760RST (Rustic)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____



Ordering Information

Product ID	9760RST
Finish	Rustic
Collection	Rustic Collection

Dimensions

Extension	7.75"
Height from center of Wall opening	5.50"
Base Backplate	5.00 DIA
Weight	3.00 LBS

Specifications

Material	Brass
Glass Description	Clear Beveled

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Wet
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	1
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

Dimensions

Height	13.25"
Width	7.00"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Alternate	INCA	60W	4071CLR	