

Dover Collection

Dover 4 Light Bath Light in Brushed Nickel

6324NI (Brushed Nickel)



Dimensions

Height	9.00"
Width	30.50"

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____

Ordering Information

Product ID	6324NI
Finish	Brushed Nickel
Available Finishes	TZ, NI
Collection	Dover Collection

Dimensions

Extension	8.00"
Height from center of Wall opening	6.25"
Base Backplate	5.00 DIA
Weight	5.80 LBS

Specifications

Material	Steel
Diffuser Description	Etched Seeded

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Damp
Warranty	www.kichler.com/warranty

Installation

Install Glass Up or Down	Yes
--------------------------	-----

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
# of Bulbs/LED Modules	4
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	G