



Item #
WC105-WH

Product Family Name:

Category:
Fan Control Systems

Certification

Patents:

Notes:

UPC Code:

Finish:
White

Category Type:
Light Kits/Accessories



Image File Name: **WC105-WH.jpg**



MEASUREMENTS

Width: 2.75"	Length: 5"	Height: 4.5	Extension:
Height Adjustable: Min Overall Height: Yes		Max Overall Height:	Slope: No
Wire Length:	Chain Length:	Safety Cable Included: No	Net Weight: 0.33
Canopy Width:	Canopy Height:	Canopy Length:	Center to Bottom:
Backplate Width: 0.00	Backplate Height: 0.00	Center to Top:	

LAMPING

No. of Bulbs: 0	Light Type:			
Max Bulb Wattage:	Socket:			
Light Kit: No	Dimmable: Yes	Ballast:	Rated Life Hours:	Uplight: No
Bulb/LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

GLASS

Description:		Material:
Part No.:		Quantity:
Width:	Height:	Length:



FAN CONTROLS

Pull Chain Control: No	Works with Remote Control: No	Works with Wall Control: No
	Included Remote Control:	Included Wall Control:
	Compatible Remote Control(s):	Compatible Wall Control(s):



SHIPPING

Carton Width:	Carton Height:	Carton Length:
Carton Weight:	Carton Cubic Feet:	Small Package Shippable: No
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: Master Pack:

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.