



S8411

F25T8/835/ENV
25 watt; T8; Fluorescent; 3500K Neutral White; 85 CRI; Medium
Bi Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8411

Item Number	Product Line	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code
S8411	HyGrade	045923084119	25	T8	Medium Bi-Pin	G13	F25T8/835/ENV
MOD In Inches	MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color
1.00"	35.78"	36"	2300	2185	20000	3500	Neutral White
Pack	CRI	Hg Content		RoHS Compliant			
30	85	3.5 mg		Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

