



48428 - GE Halogen Quartz T4 - Display Lights

Q35G8/CD

Product Photo



GENERAL CHARACTERISTICS

Base Description	2-Pin
Base Type	Pin/Plug-In
Filament	CC-2V
Rated Life Hours-nominal	1500 h
Primary Application	Display Lights <Residential>
Product Technology	Halogen
Base	G8
Bulb Shape	T4

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	10
Initial Lumens-nominal	350 lm
Color Temperature	2600 K

PRODUCT INFORMATION

Product Code	48428
Description	Q35G8/CD
Alternative Unit Of Measure	EACH
Standard Package Quantity	5
Ean UPC	043168484282
Standard Package GTIN	00043168484282
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	5
Sales Unit	Each
UCC	043168484282
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168484282
Standard Package GTIN	10043168484289
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168484282

DIMENSIONS

Diameter	0.5 in
Light Center Length	1.34 in

ELECTRICAL CHARACTERISTICS

Input Voltage [nom]	120 V
Rated power (Watts)	35 W