



60029-12: One Light Outdoor Semi-Flush Convertible Pendant



Collection: Kent

One Light Outdoor Convertible Pendant Lantern in Black Finish and Clear Beveled Glass.

Outdoor pendant finished black over die-cast aluminum with clear beveled glass. Supplied with 10" of wire.

Design #: D20030

UPC #:785652600296

Finish: Black (12)

Dimensions:

Length: 6 1/2"
Width: 6 1/2"
Height: 10 1/2"
Weight: 3.76 lbs.

Height Flush: 9 3/4"

Overall Height: 60"

Wire: 120" (color/Black)

Chain: 48"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulb Appearance: Clear

Bulbs:

1 - Medium A19 100w Max. 120v - Not included
1 - LED Medium A19 8w Max. 120v - Not included
1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Fixture is dual mount and may be installed semi-flush or as a pendant.
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Die Cast Aluminum - Black
1 Chain - Steel - Black

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

English (HC-320)
French (F-015)
Trilingual (English, Spanish, and French) (990P60_29-KEN)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Beveled	4									
Panel	Glass	Clear Beveled	4									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			7/8	5 3/16		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85

97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	60029-12	1	785652600296	8	8	13	0.481	5	93	Yes
NJ Pallet		162		48	40	75	83.333	810		No
NV Pallet		96		48	40	72	80	480		No