



Representative Image

Catalog No. AQU3182RCXAXB4

Description: PRO-STK 240V 3PH 225A NFT 18CR CU

UPC No 783175408658

Products > Panelboards > A-Series > Pro-Stock Lighting Panel

- Maximum system voltage is upto 240Vac for AQ panelboard line
- Field installable kits allow you to shift gears on the fly
- Standard Pro-Stock panels have the capability of adding sub-feed breakers or feed-thru lugs in the field
- All panel are convertible between main lugs or main breakers
- Reversible interior. No need to specify top or bottom feed
- Solid-state Spectra RMS or thermal magnetic breakers available as mains or sub-feeds
- NEMA 1 or 3R/12 enclosures available
- Flush or surface mounted trims with door within door and front hinge to box options available
- Extruded split neutrals speed and simplify wiring
- Main bus ratings of 225, 400, 600 amps available
- Modular kits allow for field installation of 200% neutrals and Service Entrance bonding straps
- Field installable TVSS (Transient Voltage Surge Suppression) kits - 200ka per phase
- Up to six poles of sub-feed available in 400A and 600A, and up to 3 poles of sub-feed available in 225A
- Meets all UL, NEMA and CSA standards

Descriptors

Category	Pro-Stock Lighting Panel
GO Schedule	32

Specifications

Voltage	240 V
Phase	3
Panel Rating	225
No of Circuits	18
Feed Thru	No
Bus	Copper
Interior Type	AQU
Box/Front Height	31.5 in
Interior Description	Pro-Stock 240V, 3PH, 225A 18Cir. CU
GSA Compliance	No