

# FA34050

## FA/LA MOLDED CASE CIRCUIT BREAKER, 480V 50A, 3P

Product availability : Stock - Normally stocked in distribution facility



Price\* : 833.00 USD



### Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Thermal-magnetic
Breaking capacity code	A

### Complementary

Line Rated Current	50 A
Poles description	3P
Breaking capacity	18 kA at 480 V AC 25 kA at 240 V AC 10 kA at 250 V DC
System Voltage	250 V DC 480 V AC
Mounting mode	I-Line
Electrical connection	I-Line connection line Lugs load
AWG gauge	AWG 14...AWG 4 (copper) 1 cable(s) AWG 12...AWG 4 (aluminium) 1 cable(s)
Terminal identifier	AL50FA
Magnetic hold current	400 A
Magnetic tripping current	850 A
Phase connection	ABC


### Environment

Product certifications	UL listed CSA
------------------------	------------------

## Ordering and shipping details

Category	01005 - FA 480V BREAKER & SWITCH
Discount Schedule	DE2
GTIN	00785901422747
Nbr. of units in pkg.	1
Package weight(Lbs)	6.169999999999999
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1304 - Schneider Electric declaration of conformity <a href="#"> Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------