



GE
Lighting

68168 - GE LED Candles

LED3DCAM-C/TP

- GE LED 25w replacement decorative candle--Soft White/Clear Finish
- GE LEDs offer outstanding energy efficiency, long-lasting performance and just-right brightness, all in one package. They're dimmable and illuminate your home with soft, warm light. Use this GE LED decorative bulb in indoor chandeliers, sconces and fixtures where the bulb is visible. Thanks to its aesthetic design, this GE LED compliments your fixture and adds a decorative touch even when the light is off. When it's turned on, GE LED's long life and low energy use will help you save money on energy.
- 25 watt replacement using only 3.5 watts
- Lasts 13.7 years based on 3 hours per day usage
- Estimated yearly energy costs \$0.42 based on 3 hours per day \$0.11 per kWh
- \$35 in energy savings over the life of the bulb based on 3 hours per day usage
- 2700K-soft white color appearance
- CAM candle shape with medium base for indoor chandeliers and decorative fixtures

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	Candle
Primary Application	Chandelier
Product Color	Clear
Product Technology	LED
Rated Life (Hours)	15000 h
10 Digit U	4316868168
Lamp Count	1
Life in Years	13.7 yr
Replacement Watts	25 W
Requested Structure	Blister - Carded
Estimated Energy Cost per Year	0.42
Base	E26
Bulb Shape	Candles

PHOTOMETRIC CHARACTERISTICS

Lumens per Watt (Efficacy)	49 lm
Nominal Initial Lumen per Watt	49
Initial Lumens-nominal	170 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	68168
Description	LED3DCAM-C/TP
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168681681
Standard Package GTIN	10043168681688
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168681681
Alternative Unit Of Measure	EACH
Standard Package Quantity	3
Ean UPC	043168681681
Standard Package GTIN	00043168681681
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	3
Sales Unit	Each
UCC	043168681681

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	3.5 W

CAUTIONS & WARNINGS

Caution

Risk of Electric Shock

- Do not open - no user serviceable parts inside
- Do not use where directly exposed to water
- Turn power off before inspection, installation, or removal
- Not intended for use with emergency exit fixtures or emergency exit lights