



98594SW-15: 18" Self-Contained 120V LED 2700K



Dimensions:

Length: 18"
Width: 3 1/2"
Height: 1"

Connection: Mounted To Box

Volts: 120

Watts: 12.75

Watts Consumed: 12.75

Watts Rated: 12.75

Hours Rated: 50000

Lumens: 817

Bulb Temp: 2700 °K

CRI: 80

Features:

- This advanced LED technology is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

Material List:

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990U9859_SW)

Collection: Self-Contained 120V LED Lighting

Ambiance Self-Contained 120V LED Lighting easily conceals under cabinets and in other areas where you need task lighting. The on-board power supply is dimmable down to 15% with electronic low voltage (ELV) and standard TRIAC dimmers. Multiple knockouts are provided along with a conduit adapter for easy link-ability and wiring for power. **Note: 12" image shown.**

Tightly clustered array of 45 premium LED chip packages bathes surfaces in consistent even illumination

Equivalent to 90-105W xenon / halogen task lights

Energy efficient - uses only 12.75 watts, 90% energy savings

Long life light source, lasts 50,000 hours

Color accurate illumination 80+ CRI, warmer white color temperature (2700K) also available in warm white color temperature (3000K)

Integrated 120 Volt power supply dims smoothly down to 15%

Low aluminum housing 1"H x 3.5"W in painted white finish also available in plated bronze or tinted aluminum finish

Integrated on off switch for independent control

Direct wire, ample KO's back and ends, romex conduit adapter included

Performance independently tested to IES LM79 standards

UPC #:785652218767

Finish: White (15)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	98594SW-15	1	785652218767	19.25	3.8	1.5	0.063	1.8	65	Yes
Master Pack	98594SW-15	10	10785652218764	20	15	4.75	0.825	19.1	65	Yes
NJ Pallet		840		48	40	71.5	79.444	1604.4		No
NV Pallet		840		48	40	71.5	79.444	1604.4		No