



S3721

40A15/F
40 watt A15 Incandescent; Frost; 2500 average rated hours;
280 lumens; Medium base; 130 volts

Features

- General Service Incandescent
- Household or Commercial use
- Long Life
- 130 volt



S3721

Item Number		UPC		Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3721		045923037214		40	A15	Medium	E26	40A15/F	130
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type		
Frost	3-1/2"	1-7/8"	C-9	280	2500	240/20	CD/1		
Dimmable/Non-Dimmable				CEC Status			RoHS Compliant		
Dimmable				Lawful for sale in California			Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

