



Ocal®

FS/FD Device Boxes & Covers-PVC Coated

T&B Catalog Number:

UPC Number: CFSRG-G
Status: 70450802043
Description: Active

PVC Coated Device Box Cover, Vertical GFCI Receptacle, Box Mount, 1 Gang, Rectangular Opening 2-21/32 Inch X 1-11/32 Inch, Raintight when used with Appropriate Box, Die Cast Aluminum, Gray

Features

Clean cover edges provide good gasket sealing

Application

For use with rigid/IMC conduits

General

T&B Replacement Catalog Number	FSKWGF1-G
Material	Aluminum
Finish	PVC Coated
Color	Gray

Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------

Packaging

Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	29.5 lbs. per 100

Application Support

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

Notes

Metric size designator (ANSI C80. 1-1994)

Dimensions are of uncoated fittings

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com