



Representative

Catalog Number: B1200HS 20EG
Product ID: 7TAA005220R0017
UPC Number: 61601309833
Status: Active

Channel, 12 Gauge, 1-5/8 Inch x 13/16 Inch, Length 20 Feet, Half Slotted Electro-Galvanized Steel with 9/16 Inch x 1-1/8 Inch Slots on 2 Inch Centers

North American Specifications (UNSPSC)

UNSPSC	30101804 Steel channels
IGCC	2577 Steel channels
Brand Name	Superstrut
Type	Metal Channels
Special Features	Designed so that the maximum number of support and framing applications can be constructed with a minimum amount of labor and pieces.
Application	Support and framing applications
Length	20 Feet
Width	1-5/8 Inch
Depth	13/16 Inch
Gauge	12
Slot Size	9/16 Inch
Material Composition	Steel
Finish	SilverGalv

European Specifications (ETIM)

ETIM	EC000386 Support/profile rail
Profile shape	U-profile
Model	Simple profile
Type of perforation	Back perforated
With toothing	N
Snap-off	N
Material	Steel
Material quality	Other
Surface protection	Other
Colour	None

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	500
Outer Dimensions (inches)	240x10.25x6.5
Weight Uom	123 lbs. per 100

Documents / Support Tools

SDS US 1	sds-00046-tb2
Technical Data Sheet US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com