



BURNDY Catalog Number GAR3902
 UPC Number 781810234013
 Description #4-4/0, 1/2-1 IPS
 Status Active

Web Use
 BURNDY Product Line

Dimensional	
Width (in)	3.25
Length (in)	1.75
Height (in)	3.5
Size (Hex) or Size (Bolt)	3/8
Size (Hex) or Size (Bolt) - in	0.38
B Length (in)	1.75
General	
Product Description	Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 1/2" - 1" Pipe, 3/8" Stud
Other	
Type of U Bolt	1031G
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467
Rated for Direct Burial	Y
Conductor(s)	
Copper Tube Size (SCH40) - Range	1/2-1
Rod Size (Range)	N/A
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	4-4/0
Rebar Size (Range)	N/A
Physical	
Type of Hardware	Steel - Galvanized
Installation Torque	200
Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Copper Alloy
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
 47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies
 47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175

