

FDS60 -- Fused Disconnect Switch

Stainless steel hardware.

Adjustable mounting feet.

Nonmetallic enclosure – safer - nonconducting.

Fused disconnect switch accepts Class "J" fuses.

Safety interlocked fuse access door.


Removable door for easier wiring.

Lockable high visibility red handle to meet OSHA Lockout/Tagout.



60A Fused Disconnect Switch

Product Specifications

Product Type	 Fused Disconnect
Switch Type	Three Pole Complete Unit
Amperage	60A
Voltage	600V AC
Operating Temperatures	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Listing and Certifications	UL Listed and CSA Certified
Weight in LBs	16.85
UPC Number	783585519609

Dimensions

