



Powering Business Worldwide

pe.eaton.com

Group Metering Main Fusible Switch

1MFS400RT

UPC:786849053666

Dimensions:

- **Height:** 15 IN
- **Length:** 48.125 IN
- **Width:** 22.625 IN

Weight:110 LB

Notes:If Class H fuse clips are needed use catalog number WCG3HK400 (order (1) per phase). If Class R fuse clips are needed order catalog number DS56FK in addition to WCG3HK400. In order to go from T to R the device must first be converted to H.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 400A
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Overhead
- **Fuse Clip Type:** Class T
- **Interrupt Rating:** 100 kAIC
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Barrier kits available 400A-800A fusible switches: Bottom feed-3MFSBBK, Top feed-3MFSTB
- **Voltage Rating:** 120/240V
- **Wire Size:** (2) #1/0-300 kcmil or (1) #750 kcmil

Supporting documents:



- Eatons Volume 1-Residential and Light Commercial
- Eaton Specification Sheet - 1MFS400RT
- Dimensional Drawing - METERING
DIMENSION DWG. FOR METER CTR. FUS.
MAINS - TOP FEED

Certifications:

- UL Listed

Product compliance: No Data