



65953-710: Three Light Pendant



Collection: Stirling

Three Light Pendant in Burnt Sienna Finish with Beige Linen Shade and Satin Etched Glass Top and Bottom Diffusers.

UPC #:785652182433

Finish: Burnt Sienna (710)

Dimensions:

Diameter: 19"

Height: 26 1/4"

Weight: 17 lbs.

Overall Height: 148 1/2"

Wire: 144" (color/Brown)

Chain: 120"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 3 - Medium A19 100w Max. 120v - Not included
- 3 - LED Medium A19 8w Max. 120v - Not included
- 3 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Material List:

1 Chain - Steel - Burnt Sienna

1 Body - Steel - Burnt Sienna

Safety Listing:

Safety Listed for Dry Locations

Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1733FS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Fabric	Beige Linen	1				9 7/8	19	1 5/8			
Diffuser	Glass	Satin Etched	1				1/8	17 1/2	13/32			
Diffuser	Glass	Satin Etched	1				1/8	17 1/2	13/32			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 3/8			5 1/2		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
--------------	-----------	----------	-----	--------	-------	--------	------	--------	-----------	----------

Individual	65953-710	1	785652182433	21.5	21.5	19.5	5.216	20.7	150	Yes
NJ Pallet		12		48	40	65	72.222	248.4		No
NV Pallet		12		48	40	65	72.222	248.4		No