



In-Wall Controls: Spring Wound Countdown Timers

FF12HHC | Spring Wound Countdown Timer - Commercial



FF12HHC

SPRING WOUND COUNTDOWN TIMER - COMMERCIAL

The FF Series Commercial Countdown Timers are designed to replace any standard wall switch and do not require electricity to operate. These energy-efficient switches automatically limit the ON times for fans, lighting, motors, heaters, and other energy consuming loads. A commercial "brushed metal" look plate (plastic construction) meets NEC requirements.



[Features & Applications](#)

Features

- No electricity required to operate

Applications

- Bathroom Fans

- Replaces any standard or decorator single-gang wall switch
- Automatically limits ON time for energy consuming loads
- Quick and easy installation
- Time-saving up front terminal connection with teeter-type terminals
- Brushed metal look switch plate meets NEC requirements (plate is included)
- Incandescent/fluorescent/CFL/LED compatible
- No neutral connection is required
- Spas
- Hot Tubs
- Storage Closets
- Garage Lights

Specifications

Color	Motor	Product Height (mm)
Brushed Metal	1 HP, 125 VAC, 50/60 Hz 2 HP, 250 VAC, 50/60 Hz	104.8
Switch Type	Operating Temperature Max (°C)	Product Width (in)
SPST	40	1.75
Countdown Time	Operating Temperature Max (F)	Product Width (mm)
12 hr	104	44.5
Hold Mode Included	Operating Temperature Min (°C)	Product Depth (in)
Yes	0	1.25
Resistive	Operating Temperature Min (F)	Product Depth (mm)
10 A, 250/277 VAC, 50/60 Hz 20 A, 125 VAC, 50/60 Hz	32	31.8
Incandescent Load Ratings (Multi-Gang)	Product Height (in)	Warranty
7 A, 125 VAC, 50/60 Hz	4.125	1-Year limited
Incandescent Load Ratings (Single-Gang)		
7 A, 125 VAC, 50/60 Hz		

For California residents, click [here](#) for Proposition 65 Warning.

Related Accessories and Parts (3)



146MT577

KNOB-WALL SWITCH FF SERIES - WHITE



146MT579

KNOB-WALL SWITCH FF SERIES - BLACK

148FD5033

**PLATE FOR 12-HR WITH HOLD (FF12HHC,
FF312HH)**