

Job Name:

Job Type:



Comments:

Quantity:

## 5DI52BSD-L: 52" Discus Fan - Brushed Steel



## Dimensions:

Diameter:	52"
Weight:	18.7 lbs.
Reverse Switch:	Manual
Rev. Switch Location:	Switch Housing
Motor Size:	153.0 X 18.0
Diameter of Housing:	11.1
Capacitor Value:	4.5+5+6/350V/85C
Lead Wire Length:	78 inches
Light Kit Included:	Yes
Remote Included:	None
Remote Group(s):	A,E

## Bulbs:

1 - Halogen Mini Candelabra T4 75w Max. 120v - included

## Features:

- Fixture is operated with a pull chain

## Material List:

## Safety Listing:

UL Listed for Dry Locations  
cUL Listed for Dry Locations

## Instruction Sheets:

English (5DI52XXD\_5DI52XXD-L-CUL-dualmount-ENG)  
French (5DI52XXD\_5DI52XXD-L-CUL-dualmount-CF)

## Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy				5 1/8		

## Blade Details:

Blade Group	Diameter	Included	RPM Hi	CFM Hi	Watts Hi	Amps Hi	RPM Med	CFM Med	Watts Med	Amps Med	RPM Low	CFM Low	Watts Low	Amps Low
	52	Yes	168.0	5209.31	64.1	0.535	113.0	3356.94	30.9	0.376	64.0	1869.93	13.3	0.247

## Mounting Options:

Mounting Type	Included	Item	Downrod Length	Downrod Diameter	Overall Height	Blade to Ceiling	Min. Ceiling Height	Canopy Style	Canopy Diameter
Downrod (Included)	yes		6.0	0.5	17.13	12.51	8.04	MC Diecast	5.12
Flush (Optional)	no	MC90-BS			11.69	5.85	7.49	MC90	5.12
Flush (Optional)	no	MC192-BS			12.9	7.06	7.59	Heavy Duty Semi-Flushmount Adapter	8.0

## Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
160-010	Frosted Glass Lens	Halogen	JDE-11	E11 Mini Candelabra	75	75	120v				

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	5DI52BSD	1	026586971459	23.5	13.25	9	1.622	22	70	Yes
NJ Pallet		48		48	40	75	83.333	1056		No
NV Pallet		48		48	40	76	84.444	984		No