



ODS15-TDW

PIR Vacancy Sensor (ManualON/AutoOFF), Vandal resistant, Manual 1 Pole Wall Switch. Robust Latching 15A Relay, No-Neutral wire required. Adjustable Service Switch: OFF/AUTO/ON (Keep in AUTO) 120/208/220/230/240/277VAC, 50/60hz, Field of View 2100 sq ft (Motion: Major 60'x40'; Minor 40'x20'), Dual Pyrometers for true 180 degree view with Blinders (32 degree block on each side). Adjustable time delay (in Adapting mode: 30s, 5/10/20m, Non-Adapting mode: 5/10/20/30m), Walk-through features. Audible Beep Warn. Light Sensor (Photocell) included for Ambient Light Hold-Off feature. Energy Code Compliant. CEC Title 20/24 compliant. NAFTA Compliant. Wall plate sold separately. Color: White

Technical Information

Product Features

Adjustment: Self-Adjusting

Code Compliance: California Title 24

Color: White

Consumption (mA): N/A

Coverage (Sq.Ft.): 2100 Sq. Ft.

Device Type: Vacancy Sensor

Grade: Commercial Specification Grade

HVAC Relay: N/A

LED Color: Red

Load Rating: 1800W@120V INC
1800VA@120V 4000VA@277V FL

Motor: 1/4 HP @ 120V

Mounting: Wall Switch

Mounting Height (Ft.): 4 Ft.

Neutral Wire Connection: Not Required

ON/OFF Configurations: Manual
ON/Auto OFF

Operating Temperature: 0°C to 50°C

Pattern: 180°

Photocell: Internal

Power Pack: External Power Pack Not Required

Product Line: ODS15

Relative Humidity: 20% to 90% non-condensing

Size: 4.06" H x 1.75" W x 1.85" D
(103.2mm x 44.4mm x 47.2mm)

Standards and Certifications: UL/cUL

Storage Temperature Range: -10°C to 85°C

Switch Type: Single-Pole

Technology: Passive Infrared

Time Adjustment: 30s-20m

Time Delay: 30s-20m

Voltage: 120/277 VAC

Wallplate: Order Separately

Warranty: 5-Year Limited

Patents*

US6031750

*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):
+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·
FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-
1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:
www.leviton.com/international/contacts/

