



PBTD INS BLK TWO SIDE TAP



- Broad wire range: 750kcmil-14
- UL listed and CSA certified for 600 volts, 90°C
- Dual rated for copper or aluminum conductor
- Cold temperature rated to -45°C
- High dielectric strength plastisol is chemical resistant
- Black cover is UV rated
- Removable port & screw plugs
- Prefilled with De-ox
- Per NEC Article 310-16 Allowable Ampacities are as follows: # 4 - 95 Amps, 1/0 - 170 Amps, 3/0 - 225 Amps, 250 - 290 Amps, 350 - 350 Amps, 600 - 475 Amps, 750 - 535 Amps
- For multiple inputs, the inputs must be staggered with outputs to allow for ampacities to be additive per NEC Table 310.16 and 310.17
- UL File E6207

Item ID	Number of Ports	Conductor Range	Length	Width	Height	Hex Size	Standard Package Quantity	NAED/UPC Number
PBTD-4-3/0	4	3/0-6 AWG	3.4200	2.2770	2.0190	1/4	6	0783669077667